

CINGHIE TRAPEZOIDALI

Quad-Power II			Cinghia trapezoidale dentellata a fianchi nudi e sezione stretta	Cinghia scanalata	Micro-V®			
	XPZ	10	8			PJ	3,60	2,34
	XPA	13	10			PL	6,40	4,70
	XPB	16	13			PM	12,50	9,40
	XPC	22	18					

Super HC® MN			Cinghia trapezoidale dentellata a fianchi nudi e sezione stretta	Cinghia trapezoidale multipla in poliuretano	Polyflex® JB™				
	SPZ	10	8			5M	5	3,30	5,30
	SPA	13	10			7M	7	5,30	8,50
	SPB	16	13			11M	11	7,10	13,20
	SPC	22	18						

Hi-Power® MN			Cinghia trapezoidale dentellata a fianchi nudi e sezione classica	Cinghia trapezoidale per trasmissioni a rapporto variabile	Multi-Speed							
	Z	10	6			W16	16,6	5,0		13	13,0	6,0
	A	13	8			W20	20,7	6,5		23	23,0	8,0
	B	17	10			W25	25,9	8,0		28	28,0	9,0
	C	22	12			W31.5	32,6	10,0		37	37,0	10,0
						W40	41,5	13,0		47	47,0	13,0
						W50	51,8	16,0				
					W63	65,3	20,0					

PowerBand®			Cinghia trapezoidale multipla	Cinghia trapezoidale per trasmissioni di grande potenza ed a frizione	PowerRated®				
	3VX	10	8	10,30			2L	1/4	1/8
	5VX	16	13	17,50			3L	3/8	7/32
	SPB	16	13	19,00			4L	1/2	5/16
	SPC	22	18	25,50			5L	21/32	3/8