



GAT4390

RENAULT/DACIA

1.2 → 2.2 & 1.6 → 2.2 D/dTi/TD



Clio, Clio II, Espace, Extra/Rapid/Express, Kangoo, Laguna, Master
Megane, Megane Scenic, R5/Van, R19, Safrane, Scenic, Symbol,
Thalia, Trafic, Twingo



1.2	D7F	700/701/710/720/722/726/730/744/746/764/766	
1.2	E7F	700/704/706/750	
1.2 16v	D4F	702/706/708/712/714/716/722/728/730/740/764	
1.4	E7J	601/624/626/634/635/680/700/706/710/711/716/718/719/720/724/ 726/728/740/742/745/754/756/757/764/770/771/773/780	} GAT3398
1.6	K7M	703/710/718/720/744/745/746	
1.8	F3P	670/682/700/704/706/708/710/712/714/720/724/755/758/760	} GAT3398
1.8 16v	F7P	704/722	
2.0	F3R	611/722/723/728/729/750/751/752/791/796/797/798	} GAT3398
2.0	J7R	732/733/734/735/768	
2.0 16v	F7R	710/714	} GAT3398
2.2	J7T	600/760/761/762/766/772/780/782	



1.6D	F8M	736/760	} GAT3398
1.9D	F8Q	600/606/620/622/624/630/632/640/644/646/648/662/672/676/678/ 680/682/684/692/696/706/714/730/732/742/744/764/706/776	
1.9D Turbo	F8Q	610/720/722/740/768/784/786/788	
1.9dTi	F9Q	710/716/717/730/731/734/736/744/770/780/782	
2.1D Turbo	J8S	620/621/622/758/760/776/778	
2.2D/Turbo	G8T	714/716/740/752/760/790/792/794	

Chrysler, Fiat/Iveco, Mitsubishi, Opel/Vauxhall & Volvo



		mm	kg
GAT4390	7468-10027	230x190x45	0.700



RENAULT/DACIA

GAT4390