



GAT4740

VOLKSWAGEN GROUP**1.6, 1.8/T, 2.0/16v/FSI****1.7SDi, 1.9D/TD/SDi/TDi**

Audi:80, A3, Cabriolet, S3, TT

A4, A6 **GAT4741**

Seat:Alhambra, Altea, Arosa, Ibiza/Cordoba, Inca, Leon, Toledo

Skoda:Fabia, Felicia, Octavia

Superb **GAT4741**

Volkswagen:Beetle, Caddy, Golf/Bora, Lupo, Polo/Classic, Sharan, Touran, Transporter

Passat **GAT4741** **GAT4844**1.61F, ABM, ADA, ADP, AEH, AEK, AFT, AHL, AKL, AKS, ALZ, ANA, APF,
ARM, AUR, AVU, AYD, BFQ, BFS, BGU, BSE, BSF

1.8ABS, ADR, ADZ, AGN, AJP, APG, APT, APX, ARG

1.8TAEB, AGU, AJH, AJL, AJQ, AMK, ANB, APP, APU, APY, AQA, AQX,
ARX, ARY, ARZ, AUM, AVC, AWC, AWT, AWU, AUQ, AYP, BAM

1.8 16vADL

2.02E, AAC, AAE, ABF, ABK, ABT, ACE, ADY, AEG, AGG, AKT, APK,
AQY, ATM, ATU, AWF, AWG, AXA, AZH, AZJ, AZL, AZM, BEH

2.0 16vABF

2.0 FSi/TFSiAXW, AXX, BGB, BHD, BLR, BLY, BMB, BPJ, PBY, BWA

 **GAT4844**

1.7SDiAHB, AHG, AKU, AKW

1.9D/Turbo1X, 1Y, AAZ, ABL, AEF

1.9SDiAEF, AEY, AGD, AGP, AQM, ASX, ASY, AYQ

1.9TDi1Z, AAZ, AFF, AFN, AGR, AHF, AHH, AHU, ALE, ALH, ASV, AVG



		mm	kg
GAT4740	7468-10016	275x240x53	1.400



5 414465 574542

