



# GAT4760B

RENAULT, NISSAN & OPEL/VAUXHALL



1.5 → 2.5dCi



## RENAULT

Avantime, Clio II, Clio III, Espace, Kangoo, Laguna, Laguna II, Master, Megane, Megane II, Modus, Scenic, Scenic II, Trafic, Twingo



|               |     |   |
|---------------|-----|---|
| 1.5 dCi ..... | K9K | 700/702/704/706/710/712/714/716/718/722/724/728/729/732/734/740/750/752/760/762/764/766/768/802/804/806             |
| 1.9dCi .....  | F9Q | 650/664/670/674/718/732/733/738/740/748/750/752/754/758/759/760/762/772/774/790/796/800/803/804/808/812/816/818/820 |
| 2.2dCi .....  | G9T | 600/605/700/702/703/706/707/710/712/720/722/742/743/750   |
| 2.5dCi .....  | G9U | 720/724/726/730/750/754   |



## NISSAN

Almera, Interstar, Kubistar, Micra K12, Note, Primastar, Primera P12, Qashqai



|              |     |                                 |
|--------------|-----|---------------------------------|
| 1.5dCi ..... | K9K | 260/270/272/274/276/702/704/710 |
| 1.9dCi ..... | F9Q | 760/762/772/774                 |
| 2.2dCi ..... | G9T | 722/750                         |
| 2.5dCi ..... | G9U | 720/724/726/750/754             |



## OPEL/VAUXHALL

Movano, Vivaro



|            |     |                                 |
|------------|-----|---------------------------------|
| 1.9D ..... | F9Q | 760/762/770/772/774             |
| 2.2D ..... | G9T | 720/750/772                     |
| 2.5D ..... | G9U | 630/632/650/720/724/730/750/754 |



|          |            |            |    |       |    |
|----------|------------|------------|----|-------|----|
|          |            |            | mm |       | kg |
| GAT4760B | 7468-10037 | 270x235x50 |    | 1.840 |    |

