



# GAT4850

ALFA ROMEO, FIAT & LANCIA



1.9JTD, 2.4JTD



## ALFA ROMEO

145, 146, 147, 156, 159, 166, Brera, GT



1.9JTD 8v .....	323.02, 371.01, 182B9.000, 937A2.000, 939A1.000, 939A2.000, 939A7.000
1.9JTD 16v .....	192A5.000, 192B1.000, 937A4.000, 937A5.000, 939A2.000, 939A8.000
2.4JTD 10v .....	325.01, 342.02, 362.02, 839A6.000, 841C.000
2.4JTD 20v .....	841G.000, 841H.000, 841M.000, 939A3.000



## FIAT

Brava/Bravo, Cromo, Doblo/Cargo, Grande Punto, Idea, Marea/Weekend, Multipla, Punto, Stilo



1.9JTD 8v .....	182B4.000, 182B9.000, 186A6.000, 188A2.000, 188A7.000, 188B2.000, 192A1.000, 192A3.000, 192A9.000, 199A5.000, 223A7.000, 939A1.000, 939A5.000, 939A7.000
1.9JTD 16v .....	192A5.000, 939A2.000, 939A8.000
2.4JTD 10v .....	185A6.000
2.4JTD 20v .....	939A3.000



## LANCIA

Kappa, Lybra, Musa, Thesis



1.9JTD 8v .....	323.02, 371.01, 188B2.000, 937A2.000
2.4JTD 10v .....	838A8.000, 839A5.000, 839A6.000, 841C.000
2.4JTD 20v .....	841G.000, 841H.000



www.gatesautocat.com

			mm		kg
GAT4850	7468-10028	230x190x45		0.900	



ALFA ROMEO, FIAT & LANCIA

GAT4850