



GAT4910

ALFA ROMEO

Twin Spark 1.4 → 2.0 16v/JTS



145, 146, 147, 155, 156, 166, GT, GTV, Spider

GAT3054-10 **GAT4519** **GAT4844**

- 1.4 16v TS335.03
- 1.6 16v TS (105CV).....372.03
- 1.6 16v TS (120CV).....312.02, 321.03, 321.04, 676.01
- 1.8 16v TS322.01, 322.05(156), 671.06
- 2.0 16v TS162.01, 323.01, 323.10, 341.03, 363.01, 672.04
- 2.0 JTS932A2.000, 937A1.000 **GAT4528**

GAT4902
Fiat 1.8 16v182A2.000, 183A1.000, 188A6.000, 192A4.000

GAT4903
Fiat 2.0/2.4 20v175A3.000, 182A1.000, 182B3.000, 182B7.000, 192A2.000



		mm	kg
GAT4910	7468-10021	230x190x45	1.250

