

1JC JETCLEAN™



↔		⊙		⌚		🚰		🏋️		📏	
-size	DN	"	"	mm	PSI	MPa	PSI	MPa	mm	kg/100m	REF.
-4	6	1/4	0.53	13.5	2900	20.0	13100	90.0	50	22	1JC04
-5	8	5/16	0.60	15.1	2900	20.0	12400	86.0	55	25	1JC05
-6	10	3/8	0.68	17.1	2900	20.0	10400	72.0	65	32	1JC06
-5	8	5/16	0.60	15.1	2900	20.0	12400	86.0	55	25	1JC05B
-6	10	3/8	0.68	17.1	2900	20.0	10400	72.0	65	32	1JC06B
-8	12	1/2	0.80	20.3	2900	20.0	9300	64.0	90	41	1JC08B
-6	10	3/8	0.68	17.1	2900	20.0	10400	72.0	65	32	1JC06G
-8	12	1/2	0.80	20.3	2900	20.0	9300	64.0	90	41	1JC08G

RECOMMENDED FOR

Use on hot and cold water high pressure cleaning equipment where heavy-duty service is required. Suited for agricultural, sports, valet and maintenance service applications.

TUBE

NBR (Nitrile) based.

REINFORCEMENT

One wire braid.

COVER

NBR/PVC based. Available in black, blue (B) and grey (G).

TEMPERATURE RANGE

-40°C to +155°C.

STANDARDS

Gates proprietary.

COUPLINGS

MegaCrimp®.

CHARACTERISTICS/BENEFITS

Grey and blue JetClean™ are suitable for use in hospitals, swimming pools and other applications where hygiene is of the utmost importance.

Premium temperature resistance up to +155°C.

IMPORTANT



Not recommended for steam service.