



# SFT001

## Stretch Fit™ Tool



### **BMW**

118, 120, 318, 320, 325, 330, 335, 520, 525, 530, 535, 635, 730, X3, X5

#### **2.0D/2.5D/3.0D**

2.0D..... M47N

2.5D..... M57N256D2 **SFT004**

3.0D..... M57N, N57N

M57306D3, M57306D4, M57306D5, M57D30A, M57N206D3, M57N2306D3, M57N306D2, M57N306D3, M57N306D5, N57N306D2, N57N306D3 } **SFT004**

### **CHRYSLER (USA)**

Grand Voyager, Voyager

#### **2.5D/2.8D**

2.5D..... EDK, ENC, ENJ

2.8D..... ENR

### **CITROËN**

C2, C3, C4, Jumper, Relay

#### **1.4D/1.6D/2.2D/3.0D**

1.4D..... DV4TD, DV4ATED, DV4ATED4

1.6D..... DV6ATED4, DV6TED4

2.2D..... 22DT

3.0D..... F30DT

### **FIAT**

Albea, Doblo, Ducato, Fiorino, Fiorino Qubo, Linea, Palio, Siena, Stilo, Strada Pick Up

#### **1.6**

1.6..... 182B6000

#### **1.3JTD/2.2D/2.3D/3.0D**

1.3JTD..... 188A, 199A, 223A

2.2D..... 4HV

2.3D..... F1AE

3.0D..... F1ACE

		mm	kg
SFT001	7468-10100	190x157x51	0.469





## FORD (EUROPE)

C-Max, Focus, Focus C-Max, Mondeo, Tourneo, Transit



**1.4/1.6/1.8/2.0**

1.4..... C14HDEZ, ZH14ASDA  
 1.6..... C16HDDZ, C16HDEZ, ZH16HWDA, ZH16HXDA  
 1.8..... C18HDEA, ZH18CSDA, ZH18Q7DA, ZH18Q7DE, ZH18Q7FA, ZH18QQDA, ZH18QQDB  
 2.0..... C20HDEA, C20HDEH, ZH20AODA, ZH20AODB, ZH20HDEA



**2.0D/2.2D**

2.0D..... ABFA, ABFB, D3FA, F3FA, FIFA  
 2.2D..... P8FA, PGFA, QVFA, QWFA



## IVECO

Daily



**2.3D/3.0D**

2.3D..... F1AE  
 3.0D..... F1CE



## MAZDA

3, 5, Axela



**1.8/2.0**

1.8..... L823  
 2.0..... LF50, LF5H, LF5W, LF72, LFD7, LFF7, LFN7, LFN8, LFZ2



## MERCEDES

Sprinter, Viano, Vito



**3.0D + GAT4843**

3.0D..... 642990, 642992, 642993



## PEUGEOT

206, 207, 307, Boxer



**1.4D/1.6D/2.2D/3.0D**

1.4D..... DV4TD, DV4ATED, DV4ATED4  
 1.6D..... DV6ATED4, DV6TED4  
 2.2D..... 22DT  
 3.0D..... F30DT



## VOLVO

C30, S40, V50



**1.6/1.8/2.0**

1.6..... B4164S3  
 1.8..... B4118S8, B4184S11  
 2.0..... B4204S3