



# GAT4848

VOLKSWAGEN GROUP



&



Camshaft Sprocket Remover



Audi: .....A4, A6, A6 Quattro, A8, Allroad, RS4, RS6, S6, S8

Skoda: .....Superb

Volkswagen: .....Passat, Phaeton, Touareg



V6 & V8

2.4 V6 30v .....AGA, AJG, ALF, ALW, AML, AMM, APC, APS, APZ, ARJ, ARN, ASM, BDV

2.7 V6 30v .....AGB, AJK, ASJ, ARE, AZA, AZB, AZR, BES

2.8 V6 30v .....ACK, AEJ, AGE, AHA, ALG, AMX, APR, AQD, ATQ, ATX, BBG

3.7 V8 40v .....AKC, AQG, BFL

4.2 V8 40v .....ANK, AQF, AQH, AQJ, ARS, ARU, ASG, AWN, AUW, AVP, AXQ, BCY, BFM, BGH, BGJ



V6

2.5TDi V6 .....AFB, AKE, AKN, AYM, BAU, BCZ, BDG, BDH, BFC

- GB** Camshaft Sprocket Remover
- F** Extracteur de pignon d'arbre à cames
- D** Nockenwellen-Werkzeugsatz
- NL** Nokkenstandwieltrekker
- E** Extractor de la rueda dentada del árbol de levas
- I** Dispositivo di rimozione della puleggia dell'albero a camme
- P** Ferramenta para remoção da roda dentada da árvore de cames
- FIN** Nokka-akselin hammaspyörän irrotin
- S** Avdragare för kamaxeldrev
- PL** Klucz do demontażu koła zębatego wałka rozrządu
- H** Vezérműtengely-kerék lehúzó
- RUS** Съемник звездочки распределительного вала
- TR** Kam mili dişli çıkarma aleti

|         |            |            |    |       |    |
|---------|------------|------------|----|-------|----|
|         |            |            | mm |       | kg |
| GAT4848 | 7468-10029 | 230x190x45 |    | 1.400 |    |

