



# GAT4960

RENAULT & NISSAN

1.4 → 2.0 16v Twin Cams



## RENAULT

Avantime, Clio II, Clio III, Espace, Kangoo, Laguna, Laguna II, Megane, Megane II, Megane Scenic, Modus, Scenic, Scenic II, Vel Satis



1.4 16v .....	K4J	700/710/711/712/713/714/715/730/732/740/750/770/780	} <b>GAT4623</b> <b>GAT4924</b>
1.6 16v .....	K4M	700/701/704/706/707/708/709/710/711/712/714/716/718/720/724/730/732/734/736/740/742/743/744/745/746/748/750/752/753/754/760/761/762/764/765/766/768/776/782/788/790/791/794/800/801/802/804/812/813/830	
1.8 16v .....	F4P	720/722/770/771/772/773/774/775	} <b>GAT4923</b>
2.0 16v/Turbo .....	F4R	700/701/712/713/714/715/720/730/732/736/738/740/741/744/746/747/760/761/762/763/764/765/766/767/770/771/774/776/784/786/787/790/792/794/795/797/830	



## NISSAN

Kubistar



1.6 16v ..... K4M

		mm	kg
GAT4960	7468-10039	230x190x45	0.900

