



FIELD BULLETIN

Carbon Free Hose Extended Range

Recommended For: Gates Carbon Free Hose is recommended for Furnace Coolant & Electrical Cable Coolant Applications in Steel Industry and other non-conductive applications.

Construction:

- **Tube:** Specialized Synthetic Rubber, Grey color.
- **Reinforcement:** High Tenacity Synthetic Yarn.
- **Cover:** Specially Compounded Nitrile, Green color.

Service Temperature Range: -40°C to +100°C

SPECIFICATIONS						
Product No.	Description	I.D.	O.D.		Working Pressure	Burst Pressure
		mm	Inch	mm	Bar	bar
33195060	3/8" Carbon Free Hose	9.5	0.67	17	17	68
33195061	2 1/4" Carbon Free hose	57	2.68	68	14	40
33195004	2 3/8" Carbon Free hose	60	2.83	72	14	40
33195062	2 3/4" Carbon Free hose	70	3.35	85	14	40
33195063	3 1/2" Carbon Free hose	89	4.17	106	14	40
36805139	4" Carbon Free hose	102	4.72	120	10	40

For more information pls contact Gates representatives.

Hoses mentioned are in import range, lead time will be 4-6 weeks.

Gates Carbon Free Hose offers high flexibility together with adequate toughness to help passing the electrical cable assembly through the hose. Gates Carbon Free Hose is specially designed and manufactured to take the abuse in your toughest working environments. You can always count on Gates Carbon Free Hose for optimal performance at a competitive price. We are The Value Connection.