

NEW

Gates' new six reel fuel line merchandiser:


Helps Maximise your Sales!

With Gates' new six reel fuel line merchandiser you can increase your market coverage. This newly designed display holds 6 reels with each of the top selling fuel line hoses on 7.5 m reels. You can choose between two different merchandisers: one with 3.2, 4, 5, 6, 8 and 10 mm inside diameter hose (ref. 4986-10160). Or one with 3.2, 4, 6, 7, 8 and 10 mm inside diameter hose (ref. 4986-10161).

Just get the range which best meets your market area requirements.

Nothing is as easy as selecting hose from this practical 6 reel display: you choose the required diameter, cut off the correct length and you have exactly what you need.

A six reel fuel line merchandiser package contains:



- a metal frame, 530 mm wide with a Gates sign and distribution plate;
- 6 reels each holding 7.5 m small diameter hose;
- seven magnetic identification plates allowing adaptation of the range to suit your needs;
- 4 screws and 4 plugs for attachment to the wall plus 2 special hooks fitting any type of pegboard;
- a Gates lightweight hose cutter tied to the frame by a light chain.

When your fuel line merchandiser needs restocking, you can order 3.2 mm, 4 mm, 5 mm, 6 mm, 7 mm and 8 mm ID hose on 15 m reels and 10 mm ID hose on a 10 m reel.




Gates' six reel fuel line hose merchandiser enhances your market coverage.



GATES AUTO MASTER





NEW

Gates' textile covered fuel line hose

Because original equipment quality is the best you can get!

Have you seen the Gates' new textile covered fuel line hose?

This high-quality hose features a durable and oil resistant textile cover providing a dependable and safe service on fuel circuits in passenger cars.

It is available in seven sizes which cover most applications and allow you to handle your customers' needs without any problem.

Programme

Prod. no	Inside diameter		Length m
	mm	inch	
4324-10050	3.2	7/64	15
4324-10051	4	5/32	15
4324-10055	5	13/64	15
4324-10052	6	1/4	15
4324-10056	7	9/32	15
4324-10053	8	5/16	15
4324-10054	10	3/8	10

For a perfect seal, use Gates hose clamps in combination with Gates' Flexi Driver. See also our catalogue E2/70326.

Applications

Designed for clamped hose applications on fuel systems in passenger cars.

Caution

Not to be used for in-tank applications, sour gas, LPG and biodiesel.

Not designed to replace coupled hose assemblies on fuel injected engines.

Construction and benefits

- The tube resists heat, fuel (leaded and unleaded petrol, diesel) and oil.
- The braided textile cover reinforces the hose and is resistant to heat, oil, ozone and weathering.
- The construction handles working pressures up to 6 kg/cm² (85 psi).
- The hose is unaffected by temperatures from -30°C to +100°C.

Your distributor:



**The world's most trusted name
in belts and hose.**