

POWERCLEAN



↔		○		○	🔥		🔧	⚖️	📏		
-size	DN	"	"	mm	PSI	MPa	PSI	MPa	mm	kg/100m	REF.
-4	6	1/4	0.53	13.5	3500	24.0	13100	90.0	100	23	4PC3500
-5	8	5/16	0.64	16.3	5000	35.0	19200	132.0	130	40	5PC5000
-6	10	3/8	0.68	17.2	3000	21.0	12000	84.0	130	33	6PC3000
-6	10	3/8	0.74	18.8	5000	35.0	19200	132.0	130	52	6PC5000
-5	8	5/16	0.59	15.1	3600	25.0	14400	100.0	130	23	5PC3600B
-5	8	5/16	0.64	16.3	5000	35.0	19200	132.0	130	40	5PC5000B
-6	10	3/8	0.68	17.2	3000	21.0	12000	84.0	130	33	6PC3000B
-6	10	3/8	0.74	18.8	5000	35.0	19200	132.0	130	52	6PC5000B
-8	12	1/2	0.80	20.3	2500	17.5	9300	64.0	180	43	8PC2500B
-8	12	1/2	0.86	21.8	4000	28.0	16000	110.0	180	62	8PC4000B
-6	10	3/8	0.68	17.2	3000	21.0	12000	84.0	130	33	6PC3000G
-6	10	3/8	0.74	18.8	5000	35.0	19200	132.0	130	52	6PC5000G
-8	12	1/2	0.80	20.3	2500	17.5	9300	64.0	180	43	8PC2500G

RECOMMENDED FOR

Use on pressure cleaning equipment. Specially compounded to handle high pressure water service.

TUBE

NBR (Nitrile) based.

REINFORCEMENT

One or two braid of high tensile steel wire.

COVER

NBR (Nitrile) based.

TEMPERATURE RANGE

-40°C to +121°C.

STANDARDS

Gates proprietary.

COUPLINGS

MegaCrimp®.

IMPORTANT



Not recommended for steam service.